## SERIES DMTFH Handheld

Series DMTFH Handheld Transit Time Ultrasonic Flow Meter is carefully designed so that it is very compact and easy to use. A user can use hand to hold as well as to operate the flow meter main unit .The user-interface is self-explanatory and very easy to follow. Besides, the unique clamp-on fixture design makes the installation very simple and no special skills or tools required. Due to the non-intrusive nature of the clamp-on technique, there is no pressure drop, no moving parts, no leaks and no contamination.



▲ Transmitter & Transducer



▲ Full set of Handheld



▲ Data logger

#### **Features:**

- 1. Compact design, light-weight and user-friendly.
- 2. Principle of Transit Time and MultiPulse<sup>TM</sup> Technology.
- 3. Can be used for mobile measurement, flow rate calibration, data comparing, meters running status checking.
- 4. A variety of liquid applications can be accommodated: ultra-pure liquids, potable water, chemicals, raw sewage, reclaimed water, cooling water, river water, plant effluent, etc.
- 5. Data Logger functions. The capacity is based on users' choice, and the maximum can reach 8GB. Users can store 5 years' data in it at least and user can read, edit and export the data for reference and analysis.

## **Applications:**

- Water (hot water, cooling water, potable water, sea water etc.)
- Petroleum products
- ◆ Chemicals, including alcohol, acids, etc
- Beverage, food and pharmaceutical processors
- Secondary sewage, waste treatment, etc.
- Power plants, Metallurgy and miming applications
- Pipeline leak detection, inspection, tracking and collection

# DYNAMETERS ...

Size	Material	Α	В	С	D
K1: 3/4", 1"	PTFE	55	39	42	34
K2: 3/4", 1", 1-1/4"	PTFE	64	46	42	43
K3: 1-1/4", 1-3/4",	PTFE	80	46	42	61



**Note:** K transducers utilize the Round-Clamp method, and the transducers' transmitting and receiving sides are connected with the pipe surface thoroughly to acquire enough coupling area, better reliability, stability, etc.

### **Principle of Measurement**

DMTF transit time flow meter utilizes two transducers that function as both ultrasonic transmitters and receivers. The transducers are clamped on the outside of a closed pipe at a specific distance from each other. The transducers can be mounted in V-method in which case the ultra sound transverses the pipe twice, or W-method in which case the ultra sound transverses the pipe four times, or in Z-method in which case the transducers are mounted on opposite sides of the pipe and the ultra sound transverses the pipe only once. The selection of mounting method depends on pipe and liquid characteristics. When the flow meter works, the two transducers transmits and receives ultrasonic signals amplified by multi beam which travels firstly downstream and then upstream (Figure 1). Because ultra sound travels faster downstream than upstream, there will be a difference of time of flight( $\triangle$  t). When the flow is still, the time difference( $\triangle$  t) is zero. Therefore, as long as we know the time of flight both downstream and upstream, we can work out the time difference, and then the flow velocity (V) and flow volume (Q) via the following formula.

**V= K\*D\*** △ t

V: Liquid velocity

K: Constant

D: Distance between the two transducers

 $\triangle$  t : Difference in time of flight




Figure 1

# DYNAMETERS...

## **Specifications**

	Power Supply	3 AAA Ni-H built-in batteries. When fully recharged it will last over 12 hours of operation. 90-240VAC for the charger				
	Velocity	0 ~ ±40 ft/s (0 ~±12m/s), bi-directional				
	Display	4 linex16 English letters LCD back lit, can display total flow, flow rate, velocity and meter running status etc.				
	Units	User Configured (English and Metric);				
	Rate	Rate and Velocity Display;				
Transmitter	Totalized	(FWD, NET, REV or BATCH) gallons, ft³, barrels, lbs, liters, m³,kg				
	Output	Frequency, RS232; options: up to 8 GB Data logger				
	Accuracy	±1.0%~2.0% of reading at rates >0.5 m/s				
		±0.005 m/s of reading at rates <0.5 m/s				
	Sensitivity	Flow Rate: 0.001ft/s (0.0003m/s)				
	Repeatability	0.2% of reading				
	Security	Keypad lockout, access code enable				
	Dimensions	100*204*34 Weight: <0.5kg				
	and Weight	100 204 34 Weight. <0.3kg				
	Liquid Types	Virtually most any liquid containing less than 2% total suspended				
	Supported	solids (TSS) or aeration				
	Suited Liquid	Std. Temp.: -40℃~121℃				
	Temperature	High Temp.: -40℃~250℃				
		Std M transducer: DN40-1000				
	Pipe Size	L transducer: DN1000-4500				
Transducer		S transducer: DN20-50				
Hansuucei		K type transducer: DN20-50				
	Dimensions	S: Size:42*25*25; weight:<0.2kg				
	and Weight	M: Size:60*43*43; weight:<0.5kg				
	and Weight	L: Size:80*53*53; weight:<1.0kg				
	Data Logger Software	Optional 512M to 8GB SD card				
		Windows-based Software Utility, data logging, data report, and				
		data curve and analyze.				

# **DYNAMETERS**

### **Parts Identification:**

#### **Parts Identification:**

**Transmitter:** 



Handheld transmitter

#### Transducer:





Mounting Frame (V method)



Mounting Frame (Z method)

#### **Accessories:**



Portable Case




Couplant



Belts

# DYNAMETERS ..

#### **DMTFH Handheld Ultrasonic Flow Meter Selection Table**



#### **Parts Number Construction example:**

DMTFH-1 2-D /DH-M-N-N-N-4m

**Description:** DMTFH Handheld ultrasonic flow meter, Frequency and RS232 output, with 90-240VAC power supply; Standard M type transducer, no mounting frame, standard temperature 40~121°C, common mounting type, 4m straight cable.

### **Data Logger and Software Utility**


#### **Features:**


- 1. Provides data logging, based on SD card data memory, the memory capacity can be 512M,1GB, 2GB, 4GB, 8GB. Normally, 1GB can store 5 years data with 5 minutes logging interval.
- 2. Very easy to read data from SD card (just plug it out from Dynameters Data Logger, and run Dynameters Data Logging and Analyze software, browse the SD card file).



▲ Data logger

3. Data report and Data Curve functions (Figure2, Figure3).





▲ Figure 2

▲ Figure 3

- 4. User can edit, generate Excel report and print it on PC (Figure 4).
- 5. Logging Parameters: Date and Time, Flow Rate, Velocity, Positive total flow, Negative total flow, Net total flow, Total Heat flow, Temperature in, Temperature out, Temperature difference and Heat flow rate.

  If user is interested in other parameters, please consult

If user is interested in other parameters, please consult us. Users can delete the unnecessary parameters from Excel Table and then print the data table.

6. Users can download the software from our website: <a href="https://www.dynameters.com">www.dynameters.com</a>


sed File Bets	Report	Beta Carre										
Dier Ties 2000W12R14B 12 44.10				×	Date Sport Fe				Test Dept			
But the Impatibility to th			16	Create Sate Sepret   Expert SE.				Test By:	Test by			
								Fire				
Salact You B												
© 44		Sm S1										
Betetie		Flor (45/3)	Fil. Selvel	MT (420	PEE 640	801 501	SFX (be)	1.1 (M)	Tie	Tiret.	1.1	
200-12	14.1	25.29	0.09	22	34		215.47		32.9	25.48	-12.78	
2010-12	14.1	20.27	0.09	20	26	E.	216.97		12.9	25.66	12.75	
2010-12	14.1	25.25	0.89	33	34	A	275.96		12.9	25.65	-12.74	
2000-02	14.1	25.44	0.09	34	36		256.31		30.9	25 45	-12.74	
2000-12	14 1	25.11	1.85	34	34	31	274.54	. 9	32.90	25.44	-12.73	
2010-12	14 1.	25.24	0.89	24	34		275.53	3	12:91	25.64	-12.12	
2010-12	14.1	25.45	0.9	34	34	9	217.16	3	32.90	25.64	-12.72	
200-12	14.1	25.54	0.9	36	34	36	279.17		12.90	25.43	-12.17	
2010-12	19.1	25.6	0.6	34.	34		217.40	10	12.91	0.42	-12.48	
2010-12	14.1	25.60	0.9	34	24	-	279.46	38	35.94	25.6	12.66	
200-12	14 1	25.98	1.9	24	34		317.16	36	12.90	25.56	-12.61	
200-12	14.1	25.5	0.9	24	34	3	215.17	38	32.9	25.56	12.61	
2010-12	14.1	IS TT	0.90	24	36		279.75	10	12.91	25.50	152.67	
2010-12	14.1	25.66	0.8	34	34	3	219.21	31	12.91	25.98	-12.86	
2009-02	19.1	25.61	0.8	34	36	3.	207.11	ju .	12.9	25.59	-12.61	
2019-12	19.1	23.46	0.9	34	34	3	29.3	31	12.9	25.99	12.67	
2000-12	14.1	25.13	0.8	34	36	0.	276.25	31	32.9	25.56	-12,67	
2001-12	18.1	25 67	0.9	34	34	16	275.36	36	12.9	25.10	12.66	
7865.15	18.7	10 M	0.9	14	766		774.10	10	let a	26.65	085	

# **DYNAMETERS**


#### **Parts & Dimensions**




**Handheld Transmitter** 



**L** Transducer



**S** Transducer



Std. M Transducer



### **DYNAMETERS**TM

Dynameters Shanghai Co., Ltd

No.751 Shulin Rd, Eastward New Area, Songjiang Industrial Zone, Shanghai 201611 Tel :( 86)21 6760 2289 Fax :( 86)21 6760 2287 E-mail: info@dynameters.com

Web: www.dynameters.com